NATIONAL GUARD DISASTER RELIEF IMMEDIATE RESPONSE ASSET

Rocky esearch

CONTAINERIZED ICE MAKER SYSTEM

Key Features

- Produces up to 3,600 lbs. of ice per day
- Automatically bags & seals in 10lb. bags
- Stores up to 1,200 lbs. of bagged ice
- Self-contained in Tricon ISO container
- Operates in 130° F environment
- Easily Transportable
- Easy to setup, operate & maintain
- Easily connects to potable water source
- Connect to 15kW generator or local power





Disaster Relief Benefits

- Supports emergent needs for ice
- Assist with food, health & medical demands
- Reduces challenges for transporting ice
- Demonstrates preparedness & coordination
- Reduces damage, hardship & loss
- Designed for use in distressed areas

Cool solutions to thermal problems. rockyresearch.com

System Specifications

Frequency:	50/60 Hz
Voltage:	208/230 VAC
Phase:	3 Phase
Power Connection:	100 AMP Class L Connector
*Fuel Usage:	22 gal. diesel or 26 gal. JP8 per 24 operational hours
Refrigerant:	R407C
Max. Ambient Temperature:	130°F / 54.4°C
Water Temperature:	40°F to 90°F / 4.4°C to 32.2°C

Physical Specifications

Form Factor:	ISO Tricon Container
Dimensions:	6' 5.5" W x 8.0' H x 8.0' D / 1.99 x 2.45 x 2.45 m
Weight:	~8,500 lbs / 3855.5 kg
**Water Supply Connection:	¾" NH-F hose bib (standard garden hose)
Water Usage:	~500 gal / 1892.7 liters per 3,600 lbs of ice
Ice Storage:	production 1200 lbs / 544.3 kg

Environmental Specifications

Ambient Temperature (Hot):	MILSTD-810G, Method 505.5 (Procedures I)	✓	COMPLETED
Solar Radiation (watts/m ²):	MILSTD-810G, Method 505.5.1	✓	COMPLETED
Ambient Humidity (Hot):	MILSTD-810G, Method 507.5	✓	COMPLETED
Fungus:	MILSTD-810, Method 508.6	~	COMPLETED
Salt Fog:	MILSTD-810G, Method 509.5	✓	COMPLETED
Blowing Dust & Sand:	MILSTD-810G, Method 510.5 (Procedures I & II)	✓	COMPLETED
Vibration:	MIL-STD-810G, Method 514.6	✓	COMPLETED
Shock:	MIL-STD-810, Methods 516.6 & 526 Rail Impact & Road March	✓	COMPLETED

*Average fuel usage when CIMS unit is powered by auxiliary 15kW generator.

**Water supply not required to be pressurized.

ICE[®] Intelligently Cooled Electronics is a registered trademark of Rocky Research. Other brands and product names are trademarks of their respective owners. Rocky Research believes the information in this publication is accurate as of its publication date. Such information is subject to change without notice and is subject to applicable technical product descriptions. Rocky Research is not responsible for inadvertent errors.